

LETTER SCALE S160



Brand: Scaleson

- Flat letter scale for weighing letters and small parcels
- For calculating the postage
- Maximum load 5 kg, division 1 g
- Easy-to-read LC display



Product Description

The letter scale is used in post offices, in the office or in the home. With the help of this small scale, you always pay the correct postage. It is particularly flat and therefore space-saving to store. The housing is made of lightweight ABS plastic.

The scale can be operated very easily with the two buttons "Tare/On" and "Off". The tare function makes it possible to determine the net weight, e.g. without packaging. With the "Unit" key, the unit can be changed from kg to lbs.

The scale can be operated with 2 AA batteries (not included). If the scale is without operation or weight change, it switches off after 90 seconds.

Functions:

Weighing, tare, overload indicator.


Low battery indicator, auto-off function

Wide range of applications...



In post offices

The letter scale S160 is particularly suitable for use in post offices. The letters can be sorted by weight or postage class before franking, making the work process much more efficient.



In the office

Even though more and more communication takes place online these days, there are still documents that need to be sent in paper form. With the letter scale S160 you are always perfectly prepared, even in the office, to make these items ready for dispatch and to frank them appropriately in no time at all.



At home

Would you like to send your family or friends a personal letter, birthday or Christmas card? No problem. With the letter scale S160 you can determine the correct postage from the comfort of your own home and frank your mail accordingly.

The special feature of our letter scale S160...



Easy to use

The scale can be operated very easily with the two keys "TARE/ON" and "OFF". The tare function allows the net weight to be determined, e.g. without packaging. With the unit key "UNIT" the unit can be changed from kg to lbs.



Easy-to-read display

The easy-to-read LC display with a digit height of 15 mm allows you to easily and conveniently read the weight values determined.



Anti-slip

The underside of the scale is equipped with four rubber feet. This always ensures a secure hold on a wide variety of surfaces.



Suspension device

When the scale is no longer needed, it can be stored hanging on the wall to save space.

[Download User instructions](#)

Technical Data

Artikelnummer	S160.02.005
Maximum load	5 kg
Division	1 g
Dimensions	242 x 170 x 39 mm
Platform size	∅ 148 mm
Anzeige	5-stelliges LC-Display
Stromversorgung	4 x AA Batterien (nicht im Lieferumfang enthalten)
Betriebstemperatur	5° – 40° C / 41° – 104° F
Wäge-Einheiten	kg/g, lb/oz